


Rotary drive ERMO-32

Part number: 2954698

FESTO

With stepper motor and integrated gear unit.



Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Size	32
Design structure	Electromechanical rotary drive With integrated gearing
Assembly position	Any
Mounting type	with internal (female) thread
Rotation angle	Endless
Gear unit ratio	7:1
Nominal torque	5 Nm
Nominal rotary speed	50 1/min
Max. speed at 90°	100 1/min
Impact energy in end positions	0.00029 J
Torsional backlash	0.2 deg
Repetition accuracy	±0,1 °
Max. axial force	450 N
Max. radial force	550 N
Permissible mass moment of inertia	0.0164 kgm ²
Product weight	2,200 g
Stepper angle at full step	1.8 deg
Stepper angle tolerance	±5 %
Mass moment of inertia, JO	0.39 kgcm ²
Duty cycle	100 %
Nominal operating voltage DC	24 V
Operating voltage DC for brake	24 V
Power consumption, brake	8 W
Brake holding torque	2.5 Nm
Mass moment of inertia of brake	0.013 kgcm ²
Nominal motor current	4.2 A
Insulation protection class	B
Motor type	Stepper motor
Rotor position sensor	Incremental encoder
Rotary position encoder interface	RS422 TTL AB-channel + zero index
Rotary position encoder measuring principle	Optical
Electrical connector system	Plug
Authorization	RCM Mark
CE symbol (see declaration of conformity)	according to EU-EMV guideline in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Interface code, base	E8-55
Protection class	IP40
Storage temperature	-20 ... 60 °C
Ambient temperature	0 ... 50 °C

Feature	Value
Relative air humidity	0 - 85 % non-condensing
PWIS conformity	VDMA24364 zone III
Materials note	Conforms to RoHS
Material flange	Wrought Aluminum alloy Anodized
Material housing	Wrought Aluminum alloy Anodized