



# Standards-based cylinder

## ESNU-8-25-P-A

Part number: 19255

FESTO

Based on DIN ISO 6432, for proximity sensing. Various mounting options, with or without additional mounting components. With elastic cushioning rings in the end positions.



### Data sheet

Feature	Value
Stroke	25 mm
Piston diameter	8 mm
Piston rod thread	M4
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Conforms to standard	CETOP RP 52 P ISO 6432
Piston-rod end	Male thread
Design structure	Piston Piston rod Cylinder barrel
Position detection	For proximity sensor
Variants	Single-ended piston rod
Operating pressure MPa	0.15 ... 1 MPa
Working pressure	1.5 ... 10 bar
Mode of operation	single-acting pushing action
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 ... 80 °C
Impact energy in end positions	0.03 J
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	24.6 N
Moving mass with 0 mm stroke	7.5 g
Additional mass factor per 10 mm of stroke	1 g
Basic weight for 0 mm stroke	35 g
Additional weight per 10 mm stroke	2.4 g
Mounting type	with accessories
Pneumatic connection	M5
Materials note	Conforms to RoHS
Material cover	Wrought Aluminum alloy neutral anodization
Material seals	NBR TPE-U(PU)
Material piston rod	High alloy steel, non-corrosive
Material cylinder barrel	High alloy steel, non-corrosive