

Micro filter LFMA-D-MINI


Part number: 192563

Classic - do not use for new projects

Without threaded connection plates with FRB threaded pin. 0.01 µm filter cartridge, with metal bowl guard.

Modern alternatives can be found by entering the first four characters of the type code in the search field.

FESTO



Data sheet

Feature	Value
Series	D
Size	Mini
Design structure	Fiber filter
Grade of filtration	0.01 µm
Condensate drain	manual rotary
Working pressure	1 ... 16 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [6:8:4] Inert gases
Air purity class at output	Compressed air in accordance with ISO8573-1:2010 [1:7:2] Inert gases
Filter efficiency	99.9999 %
Bowl guard	Metal bowl guard
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Medium temperature	1.5 ... 60 °C
Ambient temperature	-10 ... 60 °C
Residual oil content	0.01 mg/m ³
Mounting type	Line installation with accessories Optional
Assembly position	Vertical +/- 5°
Pneumatic connection, port 1	Subbase
Pneumatic connection, port 2	Subbase
Material housing	Zinc die-casting
Material filter	Boron silicate fiber
Material bowl	PC
Materials note	Conforms to RoHS