


# Flat cylinder DZF-1 5/8"- -A-P-A-S6


Part number: 194204

FESTO

Non-rotating, for position sensing, with elastic cushioning rings in end positions. Various mounting options, with or without additional mounting components.



Exemplary representation



## Data sheet

| Feature  | Value   |
|--|---|
| Stroke   | 0.04 ... 13 "   |
| Piston diameter  | 1 5/8"  |
| Max. angular deflection of piston rod +/-                | 0.6 deg   |
| Cushioning   | P: Flexible cushioning rings/plates at both ends                            |
| Mode of operation  | double-acting   |
| Protection against torque/guide                          | Oval piston   |
| Operating pressure MPa                                   | 0.1 ... 1 MPa   |
| Working pressure   | 1 ... 10 bar  |
| Operating medium   | Compressed air in accordance with ISO8573-1:2010 [7:4:4]                    |
| Note on operating and pilot medium                       | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC                  | 2 - Moderate corrosion stress   |
| PWIS conformity  | VDMA24364-B1/B2-L   |
| Ambient temperature                                      | 0 ... 120 °C  |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 633 N   |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance    | 754 N   |
| Moving mass with 0 mm stroke                             | 120 g   |
| Additional mass factor per 10 mm of stroke               | 180 g   |
| Additional weight per 10 mm stroke                       | 16 g  |
| Basic weight for 0 mm stroke                             | 480 g   |
| Pneumatic connection                                     | 1/8 NPT   |
| Material cover   | Aluminum  |
| Material seals   | FPM<br>TPE-U(PU)  |
| Material housing   | Wrought Aluminum alloy  |
| Material piston rod                                      | High alloy steel  |