

Standards-based cylinder

DSBG-160-400-PPVA-N3

Part number: 2029472

FESTO



Data sheet

| Feature | Value |
|--|---|
| Stroke | 400 mm |
| Piston diameter | 160 mm |
| Piston rod thread | M36x2 |
| Cushioning | PPV: Pneumatic cushioning adjustable at both ends |
| Assembly position | Any |
| Conforms to standard | ISO 15552 |
| Piston-rod end | Male thread |
| Design structure | Piston Piston rod Tie rod Cylinder barrel |
| Position detection | For proximity sensor |
| Variants | Single-ended piston rod |
| Operating pressure MPa | 0.06 ... 1 MPa |
| Working pressure | 0.6 ... 10 bar |
| Mode of operation | double-acting |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 ... 80 °C |
| Impact energy in end positions | 3.3 J |
| Cushioning length | 48 mm |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 11,310 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance | 12,064 N |
| Moving mass | 8,172 g |
| Moving mass with 0 mm stroke | 4,292 g |
| Additional mass factor per 10 mm of stroke | 97 g |
| Product weight | 20,071 g |
| Basic weight for 0 mm stroke | 11,751 g |
| Additional weight per 10 mm stroke | 208 g |
| Mounting type | with internal (female) thread with accessories Optional |
| Pneumatic connection | G3/4 |
| Materials note | Conforms to RoHS |
| Material cover | Coated die-cast aluminium |
| Material piston seal | NBR |
| Material piston | Die-cast aluminium |
| Material piston rod | High alloy steel |
| Material piston rod wiper seal | NBR |
| Buffer seal material | TPE-U(PU) |
| Cushion piston material | POM |
| Material cylinder barrel | Smooth-anodised wrought aluminium alloy |
| Material nut | steel, galvanized |
| Material bearing | Metal polymer compound |
| Collar nut material | Galvanized steel |
| Material tie rod | High alloy steel |