



control cable

NEBC-S1H15-E-5.0-N-LE15

Part number: 2052918
 Product to be discontinued



Type to be discontinued. Available until 2023. See Support Portal for alternative products.



Data sheet

| Feature | Value |
|------------------------------------------------------|--------------------------------------|
| Conforms to standard | DIN 47100 |
| Cable identification | Without inscription label holder |
| Electrical connection 1, function | Field device side |
| Electrical connection 1, design | Angular |
| Electrical connection 1, connection type | Plug |
| Electrical connection 1, cable outlet | Straight |
| Electrical connection 1, connection technology | Sub-D |
| Electrical connection 1, number of pins/wires | 15 |
| Electrical connection 1, occupied pins/wires | 15 |
| Electrical connection 1, type of mounting | 2x screw 4-40 UNC-2A |
| Electrical connection 2, function | Controller side |
| Electrical connection 2, connection type | Cable |
| Electrical connection 2, connection technology | Open end |
| Electrical connection 2, number of pins/wires | 15 |
| Electrical connection 2, occupied pins/wires | 15 |
| Operating voltage range DC | 0 ... 30 V |
| Nominal operating voltage DC | 24 V |
| Cable length | 5 m |
| Cable attribute | Suitable for chain link trunking |
| Bending radius, fixed cable installation | ≥ 33 mm |
| Cable diameter | 6.6 mm |
| Cable structure | 18x0,14 |
| Nominal conductor cross-section | 0.14 mm ² |
| Wire ends | Wire end ferrule |
| Protection class | IP50 |
| Note on degree of protection | in assembled condition |
| Ambient temperature | -30 ... 80 °C |
| Ambient temperature with flexible cable installation | -30 ... 80 °C |
| CE symbol (see declaration of conformity) | in accordance with EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions |
| PWIS conformity | VDMA24364-B2-L |
| Materials note | Conforms to RoHS |
| Degree of contamination | 3 |
| Material cable sheath | TPE-U(PUR) |
| Cable sheath color | Grey |