


Rotary drive ERMO-12

Part number: 2954695

FESTO

With stepper motor and integrated gear unit.



Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Size	12
Design structure	Electromechanical rotary drive With integrated gearing
Assembly position	Any
Mounting type	with internal (female) thread
Rotation angle	Endless
Gear unit ratio	9:1
Nominal torque	0.15 Nm
Nominal rotary speed	100 1/min
Max. speed at 90°	200 1/min
Impact energy in end positions	0.00002 J
Torsional backlash	0.2 deg
Repetition accuracy	±0,05 °
Max. axial force	180 N
Max. radial force	200 N
Permissible mass moment of inertia	0.0003 kgm ²
Product weight	475 g
Stepper angle at full step	1.8 deg
Stepper angle tolerance	±5 %
Mass moment of inertia, J _O	0.0079 kgcm ²
Duty cycle	100 %
Nominal operating voltage DC	24 V
Nominal motor current	0.8 A
Insulation protection class	B
Motor type	Stepper motor
Rotor position sensor	Incremental encoder
Rotary position encoder interface	RS422 TTL AB-channel + zero index
Rotary position encoder measuring principle	Optical
Electrical connector system	Plug
Authorization	RCM Mark
CE symbol (see declaration of conformity)	according to EU-EMV guideline in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Bending radius, fixed cable installation	≥ 60 mm
Interface code, base	E8-35
Protection class	IP40
Storage temperature	-20 ... 60 °C
Ambient temperature	0 ... 50 °C
Relative air humidity	0 - 85 % non-condensing
PWIS conformity	VDMA24364 zone III

Feature	Value
Materials note	Conforms to RoHS
Material flange	Wrought Aluminum alloy Anodized
Material housing	Wrought Aluminum alloy Anodized