



Linear actuator DGP-32-250-PPV-A-B

Part number: 526653

FESTO

For proximity sensing, rodless, with positive-locking connection between piston and actuator and adjustable end-position cushioning at both ends.

Type to be discontinued. Available until 2013.



Data sheet

Feature	Value
Stroke	250 mm
Piston diameter	32 mm
Cushioning	PPV: Pneumatic cushioning adjustable at both ends YSR: Shock absorber, hard characteristic curve
Assembly position	Any
Guide	Basic guide
Driver principle	positive-locking (slot)
Position detection	For proximity sensor
Working pressure	2 ... 8 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2
Ambient temperature	-10 ... 60 °C
Cushioning length	20 mm
Transverse moment M _x (graph)	2 Nm
Theoretical force at 6 bar, return stroke	483 N
Theoretical force at 6 bar, advance stroke	483 N
Moving mass	320 g
Moving mass with 0 mm stroke	320 g
Basic weight for 0 mm stroke	1,550 g
Additional mass factor per 10 mm of stroke	41 g
alternative connections	See product drawing
Pneumatic connection	G1/8
Materials information for cover	Aluminum casting coated
Materials information for seals	NBR TPE-U(PU)
Materials information, housing	Aluminum Anodized