


# Standard cylinder DNGL-32- -PPV-A

Part number: 30049

FESTO

Non-rotating, per ISO 15552, NF E 49 003.1 und UNI 10 290, for proximity sensing, with adjustable cushioning at both ends.



Exemplary representation



## Data sheet

Feature	Value
Stroke	1 ... 500 mm
Piston diameter	32 mm
Piston rod thread	M10x1,25
Based on the standard	ISO 15552 (previously also VDMA 24652, ISO 6431, NF E49 003.1, UNI 10290)
Cushioning	PPV: Pneumatic cushioning adjustable at both ends
Assembly position	Any
Piston-rod end	Male thread
Design structure	Piston Piston rod
Position detection	For proximity sensor
Variants	Single-ended piston rod
Protection against torque/guide	Square piston rod
Working pressure	0.6 ... 12 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2
Ambient temperature	-20 ... 80 °C
Cushioning length	19 mm
Theoretical force at 6 bar, return stroke	415 N
Theoretical force at 6 bar, advance stroke	483 N
Additional weight per 10 mm stroke	30 g
Basic weight for 0 mm stroke	565 g
Mounting type	with accessories
Pneumatic connection	G1/8
Materials information for cover	Aluminum
Materials information for seals	NBR TPE-U(PU)
Materials information for piston rod	High alloy steel
Materials information for cylinder barrel	Wrought Aluminum alloy