


# Coupling EAMC-B-15-22-5-5

Part number: 530085

FESTO

For electromechanical drive with stepper motor



## Data sheet

Feature	Value
Holder diameter 1	5 mm
Holder diameter 2	5 mm
Size	15
Nominal length	22 mm
Assembly position	Any
Max. speed	12,000 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 ... 60 °C
Mass moment of inertia	0.13 kgmm <sup>2</sup>
Transferable torque	1 Nm
Product weight	6 g
Materials note	Conforms to RoHS