

Positioner

CMSX-P-S-C-U-F1-D-130-C

Part number: 3929314

FESTO



Data sheet

Feature	Value
Design structure	Digital electropneumatic positioner
Mode of operation	double-acting
Design features	Safety position - pneumatic outlets closed
Assembly position	Any
Mounting type	with accessories
Measuring method: displacement encoder	Potentiometer
Sensing range	0 ... 100 deg
Display	7-segment LCD-Display With background illumination
Setting options	Via display and buttons
Size of the dead zone	0.5 ... 10 %
Operating pressure MPa	0.3 ... 0.8 MPa
Working pressure	3 ... 8 bar
Operating pressure	43.5 ... 116 psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
Standard nominal flow rate	130 l/min
Pneumatic connection	G1/8
Nominal operating voltage DC	24 V
Operating voltage range DC	21.6 ... 26.4 V
Max. current consumption	600 mA
Polarity protected	For operating voltage connections
Analog inputs, signal range	0 - 10 V 0 - 20 mA 4 - 20 mA
Analogue inputs, max. dynamic range	0 - 24 mA 0 - 11 V
Analog inputs, linearity error at 25°C	0,5%
Analog inputs, temperature coefficient	< 0.02 %FS/K
Analog inputs, resolution	16 bit
Analogue inputs, overload protection	Yes
Analog inputs, galvanic isolation	No
Analog outputs, signal range	4 - 20 mA
Analog outputs, max. load resistance	≤ 600 Ohm
Analog outputs, linearity error at 25° C	0,5%
Analogue outputs, temperature coefficient	< 0.02 %FS/K
Analog outputs, resolution	12 bit
Analogue outputs, reverse polarity protection	Yes
Analogue outputs, short circuit current rating	Yes
Analogue outputs, overload protection	Yes
Analogue outputs, galvanic isolation	No
Input characteristics	to IEC 61131-2, type 3
Switching input	PNP NPN
Digital inputs, reverse polarity protection	Yes

Feature	Value
Digital inputs, electrical isolation	Yes, via optocoupler
Digital outputs, reverse polarity protection	Yes
Switch output	3 x PNP or 3 x NPN, switchable
Digital outputs, output current	100 mA
Digital outputs, short circuit proof	Yes
Digital outputs, overload proof	Yes
Digital outputs, electrical isolation	Yes, via optocoupler
Electrical connection 1, function	3x digital output Analogue output Analogue input Digitaleingang Power supply Power supply load
Electrical connection 1, connection type	Terminal strip
Electrical connection 1, connection technology	Screwed terminal
Electrical connection 1, number of pins/wires	13
Electrical connection 1, tightening torque	0.6 Nm
Electrical connection 1, conductor cross section	< 1.5 mm ²
Cable gland connection	M20x1.5 electrical connection 1
Permissible cable diameter	7 - 13 mm electrical connection 1
Max. line length	30 m for electrical connection 1
Ambient temperature	-5 ... 60 °C
Storage temperature	-20 ... 60 °C
Relative air humidity	5 - 95 % non-condensing
Protection class	IP65
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Shock resistance	Shock test with severity level 1 in accordance with FN 942017-5 and EN 60068-2-27 as per EN 60068-2-29
Vibration resistance	Transport application test at severity level 2 in accordance with FN 942017-4 and EN 60068-2-6 as per EN 60068-2-6
Degree of contamination	3
Authorization	RCM Mark
CE symbol (see declaration of conformity)	according to EU-EMV guideline in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Material housing	Reinforced PC
Material screen	PC
Material sub-base	Anodised wrought aluminium alloy
Material shaft	High alloy steel, non-corrosive
Material coupling	High alloy steel, non-corrosive
Material screws	High alloy steel, non-corrosive
Material seals	NBR
Information on materials, cable connector	PA
Material blanking plug	PA
PWIS conformity	VDMA24364-B2-L
Materials note	Conforms to RoHS
Product weight	970 g
Dimensions W x L x H	190 mm x 105 mm x 130 mm