

Ball valve


VZBE-3/4-T-63-F-3L-F04-V15V15

Part number: 4834291

FESTO

Stainless steel, 3/2-way, nominal width 3/4", head flange F04, PN63, ASME B1.20.1 - NPT.

Festo is only a retailer of this product, not the manufacturer.



Data sheet

| Feature | Value |
|---|---|
| Design structure | 3-way ball valve L hole |
| Type of actuation | mechanical |
| Sealing principle | soft |
| Assembly position | Any |
| Mounting type | Line installation |
| Process valve connection | 3/4 NPT |
| Switching position indicator | Slot direction = flow direction |
| Flange hole pattern | F04 |
| Inside diameter | 16 mm |
| Nominal diameter DN | 20 |
| Valve function | 3/2 |
| Flow direction | reversible |
| Nominal pressure of process valve | 63 |
| Breakaway torque at differential pressure, nominal pressure, process valve PN | 14.3 Nm |
| Based on the standard | ASME B1.20.1 ISO 5211 |
| Medium | Vapour Compressed air in accordance with ISO8573-1:2010 [-:~:] Inert gases Water Neutral fluids |
| Medium temperature | -20 ... 200 °C |
| Flow rate Kv type L | 12 m3/h |
| Materials note | Conforms to RoHS |
| PWIS conformity | VDMA24364 zone III |
| Material housing | Stainless steel casting |
| Material number for housing | 1.4408 |
| Material seat seal | PTFE |
| Material seals | PTFE |
| Material ball | Stainless steel casting |
| Material number for ball | 1.4408 |
| Material shaft | High alloy steel, non-corrosive |
| Material number for shaft | 1.4401 |
| Product weight | 1,024 g |
| Authorization | CRN |
| Corrosion resistance classification CRC | 4 - Very high corrosion stress |