


Coupling

EAMD-25-22-12-10X12

Part number: 5029897

FESTO



Data sheet

Feature	Value
Holder diameter 1	12 mm
Holder diameter 2	10 mm
Size	25
Nominal length	22 mm
Assembly position	Any
Max. speed	8,000 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 ... 60 °C
Mass moment of inertia	3.2 kgmm ²
Transferable torque	9 Nm
Product weight	42.1 g
Materials note	Conforms to RoHS