


Round cylinder DSNU-S-8-30-P-A-MQ

Part number: 5205902

FESTO



Data sheet

| Feature | Value |
|--|---|
| Stroke | 30 mm |
| Piston diameter | 8 mm |
| Piston rod thread | M4 |
| Cushioning | P: Flexible cushioning rings/plates at both ends |
| Assembly position | Any |
| Design structure | Piston Piston rod Cylinder barrel |
| Position detection | For proximity sensor |
| Operating pressure MPa | 0.15 ... 1 MPa |
| Working pressure | 1.5 ... 10 bar |
| Mode of operation | double-acting |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Corrosion resistance classification CRC | 2 - Moderate corrosion stress |
| PWIS conformity | VDMA24364-B2-L |
| Cleanroom class | ISO class 6 |
| Ambient temperature | -20 ... 80 °C |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting | 22.6 N |
| Theoretical force at 0.6 MPa (6 bar, 87 psi), advance | 30.2 N |
| Moving mass with 0 mm stroke | 6.3 g |
| Additional mass factor per 10 mm of stroke | 1 g |
| Basic weight for 0 mm stroke | 20 g |
| Additional weight per 10 mm stroke | 2.4 g |
| Mounting type | with accessories |
| Pneumatic connection | M5 |
| Materials note | Conforms to RoHS |
| Material cover | Anodised wrought aluminium alloy |
| Material seals | TPE-U(PU) |
| Material piston rod | High alloy steel, non-corrosive |
| Material cylinder barrel | High alloy steel, non-corrosive |