


# Vacuum generator

## VN-05-L-T2-PQ1-VQ1-RQ1

Part number: 526114

FESTO

Standard, high suction rate, width 10 mm, T shape with push-in connector



## Data sheet

Feature	Value
Nominal size, Laval nozzle	0.45 mm
Grid dimension	10 mm
Assembly position	Any
Ejector characteristic	High suction flow rate Standard
Design structure	T-shaped
Working pressure for max. suction rate	5 bar
Working pressure	1 ... 8 bar
Nominal working pressure	6 bar
Max. suction rate with respect to atmosphere	15.7 l/min
Air supply time at nominal working pressure	1.7 s
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Medium temperature	0 ... 60 °C
Ambient temperature	0 ... 60 °C
Max. tightening torque	0.5 Nm
Product weight	15 g
Mounting type	with through hole with accessories
Pneumatic connection, port 1	QS-4
Pneumatic connection, port 3	QS-4
Vacuum connection	QS-4
Materials note	Conforms to RoHS
Material seals	NBR
Material receiver nozzle	POM
Material housing	POM-reinforced
Material transmitter nozzle	Wrought Aluminum alloy
Material fitting	Brass Nickel plated