

Vacuum generator



VN-14-L-T4-PQ3-VQ3-R02-B

Part number: 532649

★ Core product range

With ejector pulse and built-in solenoid valve. Standard, high suction rate, width 18 mm, T shape with plug connector and open silencer.

FESTO



Data sheet

Feature	Value
Nominal size, Laval nozzle	1.4 mm
Grid dimension	18 mm
Design, silencer	open
Assembly position	Any
Ejector characteristic	Standard High suction volume
Manual override	Pushing
Integrated function	Ejector pulse valve, pneumatic Electrical on-off valve Open silencer
Design structure	T-shaped
Valve function	2/2
Working pressure for max. suction rate	5 bar
Working pressure	2 ... 8 bar
Nominal working pressure	6 bar
Max. suction rate with respect to atmosphere	92.6 l/min
Air supply time at nominal working pressure	0.32 s
Operating voltage range DC	21.6 ... 26.4 V
Electrical power consumption	1.2 W
Duty cycle	100 %
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364 zone III
Medium temperature	0 ... 50 °C
Noise level at nominal operating pressure	69 dB(A)
Protection class	IP40
Ambient temperature	0 ... 50 °C
Product weight	100 g
Electrical connection	Plug
Mounting type	with through hole with top-hat rail with accessories
Pneumatic connection, port 1	QS-8
Pneumatic connection, port 3	Open silencer
Vacuum connection	QS-8
Material of connecting thread	Wrought aluminum alloy, anodized
Materials note	Conforms to RoHS
Material seals	NBR
Material receiver nozzle	POM
Material housing	PA-reinforced POM-reinforced
Material silencer	Wrought Aluminum alloy

Feature	Value
	POM PU foam
Material screws	Steel
Material transmitter nozzle	Wrought Aluminum alloy
Material fitting	Brass Nickel plated