


Standard cylinder DNGC-63- -PPV


Part number: 546031

FESTO

This product is only available via Festo Brazil.



Exemplary representation



Data sheet

Feature	Value
Stroke	1 ... 2,000 mm
Piston diameter	63 mm
Piston rod thread	M16x1,5
Based on the standard	ISO 15552 (previously also VDMA 24652, ISO 6431, NF E49 003.1, UNI 10290)
Cushioning	PPV: Pneumatic cushioning adjustable at both ends
Assembly position	Any
Piston-rod end	Male thread
Design structure	Piston Piston rod
Position detection	No
Variants	Single-ended piston rod
Working pressure	0.6 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2
Ambient temperature	-20 ... 80 °C
Cushioning length	23 mm
Theoretical force at 6 bar, return stroke	1,682 N
Theoretical force at 6 bar, advance stroke	1,870 N
Additional weight per 10 mm stroke	60 g
Basic weight for 0 mm stroke	1,825 g
Mounting type	with accessories
Pneumatic connection	G3/8
Materials information for cover	Aluminum die cast Aluminum casting
Materials information for seals	NBR TPE-U(PU)
Materials information for piston rod	High alloy steel
Materials information for cylinder barrel	Wrought Aluminum alloy