


Handling module HSP-16-AP-SD-WR

Part number: 533609

FESTO

with semi-rotary drive, protective cover and wait position module on right.



Data sheet

Feature	Value
Size	16
Maximum Z-stroke, wait position	25 mm
Y stroke	90 ... 110 mm
Z stroke	35 ... 50 mm
Z stroke, working stroke	20 mm
Cushioning	CC: Shock absorber at both ends Soft characteristic
Assembly position	Guide rail Vertical
Mode of operation	double-acting
Design structure	Cross-guide Swivel module Wait position alternatively on left guided motion sequence
Position detection	For proximity sensor
Protection against torque/guide	Cross-guide
Working pressure	4 ... 8 bar
Minimum cycle time	0.8 s
Repetition accuracy	±0,01 mm
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364-B2-L
Ambient temperature	0 ... 60 °C
Max. torque Mx dynamic	2.4 Nm
Max. torque Mx static	10 Nm
Max. torque My dynamic	2.4 Nm
Max. torque My static	10 Nm
Max. torque Mz dynamic	2.4 Nm
Max. torque Mz static	10 Nm
Maximum effective load	1 kg
Theoretical force at 0.6 MPa (6 bar, 87 psi)	50 N
Product weight	4,600 g
Mounting of front unit	with through hole
Mounting type	with through hole With slot nuts
Pneumatic connection, wait position	M5
Pneumatic connection	M5
Material sub-base	Wrought Aluminum alloy
Material cross-guide	Heat-treatment steel
Material side components	Wrought Aluminum alloy