


Activated carbon filter

MS12-LFX-G-U

Part number: 537155

FESTO

Metal bowl, direction of flow: from left to right.



Data sheet

Feature	Value
Size	12
Series	MS
Assembly position	Vertical +/- 5°
Condensate drain	manual rotary
Design structure	Fiber filter
Bowl guard	integrated as metal shell
Working pressure	0 ... 20 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [1:4:2] Inert gases
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	-10 ... 60 °C
Air purity class at output	Compressed air to ISO 8573-1:2010 [1:4:1]
Medium temperature	5 ... 30 °C
Residual oil content	≤ 0.003 mg/m ³
Ambient temperature	-10 ... 60 °C
Product weight	7,000 g
Mounting type	Line installation With mounting bracket Optional
Material of cover	PA
Materials note	Conforms to RoHS
Material seals	NBR
Material filter	Active carbon Fiber
Material housing	Aluminum die cast
Material bowl	Wrought Aluminum alloy
Material screen	PC