


# Compact cylinder ADNGF-20-10-P-A

Part number: 554221

FESTO

According to ISO 21287, with plain-bearing guide, piston rod secured against rotation by means of guide rods and yoke plate.



## Data sheet

Feature	Value
Stroke	10 mm
Piston diameter	20 mm
Based on the standard	ISO 21287
Cushioning	P: Flexible cushioning rings/plates at both ends
Assembly position	Any
Design structure	Piston Piston rod Profile barrel
Position detection	For proximity sensor
Protection against torque/guide	Guide rod with yoke
Operating pressure MPa	0.15 ... 1 MPa
Working pressure	1.5 ... 10 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 ... 80 °C
Impact energy in end positions	0.2 J
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	141 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	188 N
Moving mass with 0 mm stroke	60 g
Additional mass factor per 10 mm of stroke	11 g
Basic weight for 0 mm stroke	161 g
Additional weight per 10 mm stroke	26 g
Pneumatic connection	M5
Materials note	Conforms to RoHS
Material of flange screw	Steel
Material cover	Anodised wrought aluminium alloy
Material seals	TPE-U(PUR)
Material end plate	Anodised wrought aluminium alloy
Material piston rod	High alloy steel
Material cylinder barrel	Smooth-anodised wrought aluminium alloy