



# Electro-cylinder DNCE-40- -LS-2,5-Q

Part number: 545213

FESTO

mit Gleitgewindetrieb und verdrehgesicherter Kolbenstange.



## Data sheet

Feature	Value
Working stroke	1 ... 600 mm
Size	40
Stroke reserve	0 mm
Piston rod thread	M12x1,25
Reversing backlash	0.2 mm
Spindle diameter	12.5 mm
Spindle pitch	2.5 mm/U
Max. angular deflection of piston rod +/-	0.25 deg
Based on the standard	ISO 15552 (bisher auch VDMA 24652, ISO 6431, NF E49 003.1, UNI 10290)
Assembly position	Any
Motor type	Stepper motor DC servo motor
Position detection	für Näherungsschalter
Design structure	Elektrozylinder mit Gleitgewindespindel
Spindle type	Plain thread
Variants	verdrehgesicherte Kolbenstange
Protection against torque/guide	with plain-bearing guide
Max. acceleration	1 m/s <sup>2</sup>
Max. speed	0.07 m/s
Repetition accuracy	+/-0,07 mm
Duty cycle	100%
Corrosion resistance classification CRC	0
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	0 ... 50 °C
Impact energy in end positions	0.0002 J
Permanent drive torque	1.15 Nm
Permanent feed force	600 N
Max. drive torque	1.15 Nm
Max. torque for protection against rotation	4 Nm
Max. torque M <sub>x</sub>	4 Nm
Max. radial force at drive shaft	120 N
Max. feed force F <sub>x</sub>	600 N
No-load driving torque	0.15 Nm
Reference value for working load, horizontal	60 kg
Reference value for working load, vertical	30 kg
Mass moment of inertia J <sub>H</sub> per metre of stroke	0.1341 kgcm <sup>2</sup>
Mass moment of inertia J <sub>L</sub> per kg of working load	0.0016 kgcm <sup>2</sup>
Mass moment of inertia, J <sub>O</sub>	0.1316 kgcm <sup>2</sup>
Moving mass with 0 mm stroke	250 g
Additional weight per 10 mm stroke	46.1 g
Basic weight for 0 mm stroke	1,210 g
Additional mass factor per 10 mm of stroke	8.9 g

Feature	Value
Mounting type	with internal (female) thread with accessories
Materials note	Contains PWIS substances
Materials information for cover	Aluminium casting Painted
Materials information for seals	NBR
Materials information, housing	Wrought Aluminium alloy Smooth anodised
Materials information for piston rod	High alloy steel, non-corrosive
Material information, spindle nut	POM
Material information, spindle	Steel
Materials information for cylinder barrel	Wrought Aluminium alloy Smooth anodised