



Solenoid valve

VOFC-L-M32C-MC-G14-1K4-EX3A

Part number: 562878

FESTO



Data sheet

Feature	Value
Valve function	3/2 closed, monostable
Type of actuation	electrical
Width	51 mm
Standard nominal flow rate	900 l/min
Working pressure	2 ... 8 bar
Design structure	Pilot-actuated piston poppet valve
Type of reset	mechanical spring
Protection class	IP65
Nominal size	6 mm
Sealing principle	soft
Assembly position	Any
Manual override	None
Type of piloting	Piloted
Pilot air supply	external Internal
Flow direction	non reversible
Safety Integrity Level (SIL)	up to SIL4 High Demand mode up to SIL4 Low Demand mode
Note on working pressure	0 - 8 bar with external pilot air
Flow rate Kv ventilation	0.72 m ³ /h
Flow rate Kv exhaust	1.38 m ³ /h
Switching time off	12 ms
Switching time on	20 ms
Duty cycle	100%
Required current consumption	16 mA
Max. input power	1.2 W
Max. input voltage	32 V
Max. input current	0.2 A
Characteristic coil data	14 V DC - 32 V DC
ATEX category Gas	II 2G
Explosion ignition protection type Gas	Ex ia IIC T6, T5
Explosion-proof ambient temperature	T5: -30°C ≤ Ta ≤ +65°C T6: -30°C ≤ Ta ≤ +50°C
Certificate issuing department	PTB 08 ATEX 2038
Operating medium	Compressed air in accordance with ISO8573-1:2010 [-:-:-]
CE symbol (see declaration of conformity)	according to EU-Ex protection guideline (ATEX)
Corrosion resistance classification CRC	4
Medium temperature	-25 ... 60 °C
Product weight	880 g
Electrical connection	Terminal box, cable entry thread M20x1.5
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 2	G1/4
Pneumatic connection, port 3	G1/4
Materials note	Contains PWIS substances Conforms to RoHS
Materials information for seals	NBR
Materials information, housing	Aluminum Hard Ematal plated