


Filter MS9-LF-G-EUV

Part number: 564107



40 µm filter, metal bowl guard, fully automatic condensate drain, flow direction from left to right.



Data sheet

Feature	Value
Size	9
Series	MS
Assembly position	Vertical +/- 5°
Grade of filtration	40 µm
Condensate drain	fully automatic
Design structure	Sintered filter with centrifugal separator
Max. condensate volume	220 ml
Working pressure	2 ... 12 bar
Explosion-proof ambient temperature	-10°C ≤ Ta ≤ +60°C
Operating medium	Compressed air to ISO 8573-1:2010 [7:9:-] Inert gases
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Storage temperature	5 ... 60 °C
Air purity class at output	Compressed air in accordance with ISO8573-1:2010 [7:8:4]
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Product weight	2,000 g
Mounting type	Line installation with accessories Optional
Material of cover	PA-reinforced
Material of spin disc	POM
Material of filter holder	POM
Materials note	Conforms to RoHS
Material of connecting plate	Aluminum die cast
Material mounting bracket	Aluminum die cast
Material filter	PE
Material housing	Aluminum die cast
Material module connector	Aluminum die cast
Material bowl	Wrought Aluminum alloy
Material cup seal	NBR
Material screen	PA
Material separating plate	POM