


Manifold strip VABM-L1-14S-G14-10

Part number: 566626

★ Core product range

FESTO



Data sheet

Feature	Value
Grid dimension	16 mm
Max. number of valve positions	16
Operating pressure MPa	-0.09 ... 1 MPa
Working pressure	-0.9 ... 10 bar
Authorization	RCM Mark c UL us - Recognized (OL)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Max. tightening torque, H-rail mounting	1.5 Nm
Max. tightening torque, valve mounting	0.65 Nm
Max. tightening torque, wall mounting	3 Nm
Product weight	446 g
Pneumatic connection, port 1	G1/4
Pneumatic connection, port 3	G1/4
Pneumatic connection, port 5	G1/4
Materials note	Conforms to RoHS
Material manifold	Wrought Aluminum alloy