

Fine filter MS9-LFM

Part number: 552940

FESTO

For manifold assembly, with G thread.



Exemplary representation

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Series	MS
Size	9
Design structure	Fiber filter
Grade of filtration	0.01 ... 1 µm
Condensate drain	fully automatic manual momentary-contact manual rotary semi-automatic
Working pressure	0 ... 20 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [6:8:4]
Max. condensate volume	225 ml
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Medium temperature	-10 ... 60 °C
Ambient temperature	-10 ... 60 °C
Differential pressure display	Visual indicator
Authorization	c UL us - Recognized (OL)
CE symbol (see declaration of conformity)	according to EU-Ex protection guideline (ATEX)
UKCA marking (see declaration of conformity)	To UK EX instructions
Explosion protection certification outside the EU	EPL Db (GB) EPL Gb (GB)
ATEX category Gas	II 2G
ATEX category Dust	II 2D
Explosion ignition protection type Gas	Ex h IIC T6 Gb X
Explosion ignition protection type Dust	Ex h IIIC T60°C Db X
Explosion-proof ambient temperature	+5°C ≤ Ta ≤ +60°C
Mounting type	Line installation with accessories Optional
Assembly position	Vertical +/- 5°
Pneumatic connection, port 1	Manifold module G1/2 G3/4 G1 G1 1/4 G1 1/2 1/2 NPT 3/4 NPT 1 NPT 1 1/4 NPT 1 1/2 NPT
Pneumatic connection, port 2	Manifold module

Feature	Value
	G1/2 G3/4 G1 G1 1/4 G1 1/2 1/2 NPT 3/4 NPT 1 NPT 1 1/4 NPT 1 1/2 NPT