



# Pressure transmitter

## SPTE-V1R-F-V-2.5K

Part number: 571478

FESTO



## Data sheet

Feature	Value
Authorization	RCM Mark c UL us - Recognized (OL)
CE symbol (see declaration of conformity)	according to EU-EMV guideline in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Certificate issuing department	UL E322346
Materials note	Conforms to RoHS
Measured variable	Relative pressure
Measurement method	Piezoresistive pressure sensor
Pressure measuring range start value (MPa)	0 MPa
Pressure measuring range, initial value	0 bar
Pressure measuring range start value (psi)	0 psi
Pressure measuring range end value (MPa)	-0.1 MPa
Pressure measuring range, final value	-1 bar
Pressure measuring range end value (psi)	-14.5 psi
Overload pressure	0.5 MPa 5 bar
Overload pressure (psi)	72.5 psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible
Medium temperature	0 ... 50 °C
Ambient temperature	0 ... 50 °C
Accuracy, FS	3 %FS
Repetition accuracy in ± %FS	0.3 %FS
Temperature co-efficient in ± %FS/K	0.05 %FS/K
Analog output	0 - 10 V
Rise time	1 ms
Min. load resistance, voltage output	15 kOhm
Short circuit strength	for all electrical connections
Operating voltage range DC	18 ... 30 V
Polarity protected	for all electrical connections
Electrical connection	3-core Cable Open end
Cable length	2.5 m
Mounting type	With through-hole and screw
Assembly position	Any
Pneumatic connection	Flange
Product weight	35 g
Material housing	PA-reinforced
Material sealing ring	FPM
Protection class	IP40
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Cleanroom class	ISO class 4