


# Proximity Sensor SIEF-M30B-PS-K-L

Part number: 553550

FESTO

With cable, flush mounting



## Data sheet

Feature	Value
Design	Round
Conforms to standard	EN 60947-5-2
Authorization	RCM Mark c UL us - Listed (OL)
CE symbol (see declaration of conformity)	according to EU-EMV guideline
Materials note	Conforms to RoHS
Nominal switching distance	10 mm
Ambient temperature	-30 ... 70 °C
Repetition accuracy	0.55 mm
Switch output	PNP
Switching element function	Normally open contact
Max. switching frequency, DC	2,000 Hz
Max. output current	200 mA
Short circuit strength	Pulsing
Operating voltage range DC	10 ... 30 V
Polarity protected	for all electrical connections
Electrical connection	3-core Cable
Cable length	2.5 m
Material cable sheath	TPE-U(PU)
Size	M30
Type of installation	flush
Product weight	191 g
Material housing	Brass TPE-O Chromed-plated
Operating status display	Yellow LED
Ambient temperature with flexible cable installation	-5 ... 70 °C
Protection class	IP68
Interference immunity to magnetic fields	DC and AC magnetic field
Surge strength	0.8 kV
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Degree of contamination	3