



Mini slide

EGSL-BS-45-200-10P

Part number: 559336

FESTO



Data sheet

| Feature | Value |
|--|--|
| Working stroke | 200 mm |
| Size | 45 |
| Parallel running in the z-direction | 0.08 mm |
| Parallelism | 0.1 mm |
| Reversing backlash | $\leq 50 \mu\text{m}$ |
| Spindle diameter | 10 mm |
| Spindle pitch | 10 mm/U |
| Assembly position | Any |
| Guide | Ball bearing cage guide |
| Design structure | Electric mini slide Guide With ball screw |
| Motor type | Stepper motor Servomotor |
| Spindle type | Ball screw |
| Position detection | For proximity sensor |
| Max. acceleration | 25 m/s ² |
| Max. speed | 1 m/s |
| Repetition accuracy | $\pm 0,015 \text{ mm}$ |
| Duty cycle | 100 % |
| Corrosion resistance classification CRC | 0 - No corrosion stress |
| PWIS conformity | VDMA24364 zone III |
| Sound pressure level | 60 dB(A) |
| Protection class | IP40 |
| Ambient temperature | 0 ... 60 °C |
| Permanent feed force | 100 N |
| Max. drive torque | 0.51 Nm |
| Max. force F _y | 291 N |
| Max. force F _z | 291 N |
| Max. torque M _x | 14.3 Nm |
| Max. torque M _y | 12.3 Nm |
| Max. torque M _z | 12.3 Nm |
| Max. radial force at drive shaft | 120 N |
| Max. feed force F _x | 150 N |
| No-load driving torque | 0.08 Nm |
| Reference value for working load, horizontal | 6 kg |
| Reference value for working load, vertical | 6 kg |
| Mass moment of inertia J _L per kg of working load | 0.0253 kgcm ² |
| Mass moment of inertia, J _O | 0.0731 kgcm ² |
| Feed constant | 10 mm/U |
| Maintenance interval | Life-time lubrication |
| Moving mass | 940 g |
| Product weight | 2,190 g |
| Mounting type | with internal (female) thread with centering sleeve with accessories |

| Feature | Value |
|----------------------|------------------------------------|
| Materials note | Conforms to RoHS |
| Material cover | Aluminum casting Painted |
| Material guide rail | Roller bearing steel |
| Material housing | Wrought Aluminum alloy Anodized |
| Material yoke plate | Wrought Aluminum alloy Anodized |
| Material spindle nut | Roller bearing steel |
| Material spindle | Roller bearing steel |