



Three-point gripper HGDT-63-A-F-G2

Part number: 560191

FESTO

Sturdy, can be used as internal and external gripper, for position sensing. With gripping force retention when closing...-G2.



Data sheet

Feature	Value
Size	63
Stroke per gripper jaw	5 mm
Max. replacement accuracy	≤ 0.2 mm
Max. angular gripper jaw backlash ax,ay	≤ 0.1 deg
Max. gripper jaw backlash Sz	≤ 0.05 mm
Rotationally symmetrical	≤ 0.2 mm
Repetition accuracy, gripper	≤ 0.03 mm
Number of gripper fingers	3
Assembly position	Any
Mode of operation	double-acting
Gripper function	3-point
Gripper force back-up	On closing
Design structure	Inclined plane guided motion sequence
Position detection	For proximity sensor
Working pressure	4 ... 8 bar
Working pressure, sealing air	0 ... 0.5 bar
Max. operating frequency of gripper	≤ 4 Hz
Min. opening time at 0.6 MPa (6 bar, 87 psi)	169 ms
Min. closing time at 0.6 MPa (6 bar, 87 psi)	128 ms
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Ambient temperature	5 ... 60 °C
Mass moment of inertia	39.5 kgcm ²
Max. force on gripper jaw Fz static	2,500 N
Max. torque at gripper Mx static	80 Nm
Max. torque at gripper My static	50 Nm
Max. torque at gripper Mz static	60 Nm
Lubrication interval for guide components	5 Mio SP
Max. mass per external gripper finger	250 g
Product weight	2,543 g
Mounting type	With through-hole and dowel pin With internal thread and dowel pin Optional
Pneumatic connection, sealing air	M5
Pneumatic connection	G1/8
Materials note	Conforms to RoHS
Material cover cap	High alloy steel, non-corrosive
Material housing	Wrought Aluminum alloy COMPCOTE coated
Material gripper jaws	Steel, hardened