


Pneumatic valve VUWS-25

Part number: 8022015

FESTO



Exemplary representation

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Valve function	2x3/2 closed, monostable 2x3/2 open, monostable 2x3/2 open/closed, monostable 3/2 closed, monostable 3/2 open, monostable 5/2 bistable 5/2 monostable 5/3 pressurized 5/3 exhausted 5/3 closed
Type of actuation	pneumatic
Valve size	26.5 mm
Standard nominal flow rate	1,000 ... 1,300 l/min
Working pressure	-0.9 ... 10 bar
Design structure	Piston slide Poppet seat
Type of reset	mechanical spring Air spring
Authorization	c UL us - Recognized (OL)
Exhaust-air function	throttleable
Sealing principle	soft
Assembly position	Any
Manual override	None
Type of piloting	direct
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Pilot medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Mounting type	on manifold rail with through hole Optional
Scavenging orifice connection	Non-ducted
Materials note	Conforms to RoHS
Material housing	Aluminum die cast Painted
Material screws	Galvanized steel