


Solenoid valve

VSVA-B-T32N-AZH-D2-1T1L

Part number: 8034977

FESTO



Data sheet

| Feature | Value |
|---|--|
| Valve function | 2x3/2 closed, monostable |
| Type of actuation | electrical |
| Width | 52 mm |
| Standard nominal flow rate | 2,400 l/min |
| Operating pressure MPa | -0.09 ... 1 MPa |
| Working pressure | -0.9 ... 10 bar |
| Design structure | Piston slide |
| Authorization | c UL us - Recognized (OL) |
| KC mark | KC-EMV |
| CE symbol (see declaration of conformity) | according to EU-EMV guideline |
| Protection class | IP65 NEMA 4 |
| Grid dimension | 59 mm |
| Exhaust-air function | throttleable Via throttle plate Via individual sub-base |
| Sealing principle | soft |
| Assembly position | Any |
| Conforms to standard | ISO 5599-2 |
| Manual override | Pushing |
| Type of piloting | Piloted |
| Pilot air supply | external |
| Flow direction | reversible only |
| Signal status display | LED |
| Pilot pressure MPa | 0.3 ... 1 MPa |
| Pilot pressure | 3 ... 10 bar |
| Flow rate of valve | 3,000 l/min |
| Flow rate of valve on individual subbase | 2,600 l/min |
| Flow rate of pneumatically linked valve | 2,400 l/min |
| Switching time off | 30 ms |
| Switching time on | 30 ms |
| Duty cycle | 100 % |
| Max. positive test pulse with logic 0 | 1,000 µs |
| Max. negative test pulse with logic 1 | 3,500 µs |
| Nominal breakaway current per solenoid coil | 165 mA up to 30 ms |
| Nominal current with current reduction | 35 mA after 30 ms |
| Characteristic coil data | 24 V DC: 4.6 W |
| Surge strength | 2.5 kV |
| Degree of contamination | 3 |
| Permissible voltage fluctuation | +/- 10 % |
| Operating medium | Compressed air in accordance with ISO8573-1:2010 [7:4:4] |
| Note on operating and pilot medium | Lubricated operation possible (subsequently required for further operation) |
| Vibration resistance | Transport application test at severity level 2 in accordance with FN 942017-4 and EN 60068-2-6 |

| Feature | Value |
|---|---|
| Shock resistance | Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27 |
| Corrosion resistance classification CRC | 0 - No corrosion stress |
| PWIS conformity | VDMA24364-B1/B2-L |
| Medium temperature | -5 ... 50 °C |
| Relative air humidity | 0 - 90 % |
| Ambient temperature | -5 ... 50 °C |
| Product weight | 740 g |
| Electrical connection | Plug-in as per ISO 5599-2 |
| Mounting type | On subbase |
| Auxiliary pilot air port 12/14 | Connection plate size 2 as per ISO 5599-2 |
| Pilot exhaust port 82/84 | Optional Not ducted as per standard Ducted |
| Pneumatic connection, port 1 | Connection plate size 2 as per ISO 5599-2 |
| Pneumatic connection, port 2 | Connection plate size 2 as per ISO 5599-2 |
| Pneumatic connection, port 3 | Connection plate size 2 as per ISO 5599-2 |
| Pneumatic connection, port 4 | Connection plate size 2 as per ISO 5599-2 |
| Pneumatic connection, port 5 | Connection plate size 2 as per ISO 5599-2 |
| Materials note | Conforms to RoHS |
| Material seals | FPM HNBR NBR |
| Material housing | Aluminum die cast PA |
| Material screws | Galvanized steel |