



# flow transmitter SFTE-

Part number: 8035301

FESTO



Exemplary representation

## Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Authorization	RCM Mark
CE symbol (see declaration of conformity)	according to EU-EMV guideline in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
KC mark	KC-EMV
Materials note	Conforms to RoHS
Measured variable	Mass flow rate Volumetric flow rate
Direction of flow	Unidirectional
Measuring principle	Thermal
Measurement method	Heat Loss
Flow rate detection range, start value	0 l/min
Flow rate detection range, end value	1 ... 10 l/min
Working pressure	-0.9 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [6:4:4] Nitrogen
Medium temperature	0 ... 50 °C
Ambient temperature	0 ... 50 °C
Nominal temperature	23 °C
Repetition accuracy in ± %FS	1 %FS
Analog output	0 - 10 V 1 - 5 V
Rise time	3 ms
Min. load resistance, voltage output	20 kOhm
Short circuit strength	Yes
Overload withstand capability	Available
Operating voltage range DC	22 ... 26 V
Idle current	≤ 17 mA
Polarity protected	for all electrical connections
Electrical connection 1, connection type	Cable Cable with plug
Electrical connection 1, connection technology	M8x1, A-coded to EN 61076-2-104 Open end
Electrical connection 1, number of pins/wires	3
Cable length	0.3 ... 2.5 m
Material cable sheath	TPE-U(PUR)
Mounting type	Line installation with through hole with accessories
Assembly position	Any
Pneumatic connection	Female thread M5 For push-in connector outside diameter 3 mm For push-in connector outside diameter 4 mm

<b>Feature</b>	<b>Value</b>
Product weight	17 ... 40 g
Material housing	PA-reinforced
Protection class	IP40
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L