



Vacuum generator

VABF-S4-2-V2B1-G38-CB-VL-20-A

Part number: 8067141

FESTO



Data sheet

Feature	Value
Width	35 mm
Nominal size, Laval nozzle	2 mm
Design, silencer	open
Type of actuation	electrical
Polarity protected	for all electrical connections
Assembly position	Any
Ejector characteristic	High suction flow rate Standard
Manual override	detenting Pushing Covered
Integrated function	Ejector pulse, electrical Flow control valve Electrical on-off valve Air saving function, electrical Non-return valve Open silencer Vacuum switch
Measured variable	Relative pressure
Measuring principle	Piezoresistive
Switching function	Window comparator Threshold value comparator
Valve function	5/3 pressurized
Type of display	LED LED display 2-digit
Unit(s) that can be displayed	kPa
Threshold value setting range	0 ... 99 kPa
Hysteresis setting range	0 ... 90 kPa
Setting options	Teach-In Via parameter sets
Signal status display	LED
Switching status display sensor	LED
Working pressure for max. suction rate	5 bar
Working pressure	4 ... 8 bar
Nominal working pressure	6 bar
Pilot pressure	4 ... 10 bar
Max. suction rate with respect to atmosphere	179 l/min
Air supply time at nominal working pressure	0.2 s
Operating voltage range DC	21.6 ... 30 V
Idle current	30 mA
Duty cycle	100 %
Authorization	RCM Mark
CE symbol (see declaration of conformity)	according to EU-EMV guideline
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible

Feature	Value
Corrosion resistance classification CRC	0 - No corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Medium temperature	-5 ... 50 °C
Noise level at nominal operating pressure	61 dB(A)
Protection class	IP65
Safety class	III
Ambient temperature	-5 ... 50 °C
Product weight	955 g
Pressure measuring range	-1 ... 0 bar
Display range, start value	0 kPa
Display range, end value	99 kPa
Accuracy, FS	3 %FS
Switching point reproducibility, FS	1 %
Electrical connection	Fieldbus via CPX
Pneumatic connection, port 3	Open silencer
Vacuum connection	G3/8
Materials note	Conforms to RoHS
Material seals	HNBR NBR
Material receiver nozzle	POM
Material housing	Wrought Aluminum alloy
Material plate	Aluminum die cast
Material adjusting screw	High alloy steel, non-corrosive
Material silencer	POM PU foam
Material screws	Steel
Material transmitter nozzle	Wrought Aluminum alloy