

Electro-cylinder ESBF-BS-80-100-15P

Part number: 574107

FESTO

With ball screw, electrically actuated spindle that converts the rotary motion of the motor into linear motion of the piston rod.



Data sheet

Feature	Value
Size	80
Stroke	100 mm
Piston rod thread	M20x1,5
Reversing backlash	30 µm
Spindle diameter	32 mm
Spindle pitch	15 mm/U
Max. angular deflection of piston rod +/-	0.5 deg
Based on the standard	ISO 15552
Assembly position	Any
Piston-rod end	Male thread
Motor type	Servomotor
Position detection	For proximity sensor
Design structure	Electro-cylinder with ball screw
Spindle type	Ball screw actuator
Protection against torque/guide	with plain-bearing guide
Max. acceleration	15 m/s ²
Max. speed	0.7 m/s
Repetition accuracy	±0,01 mm
Duty cycle	100 %
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364 zone III
Storage temperature	-20 ... 60 °C
Food-safe	See Supplementary material information
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	0 ... 60 °C
Max. drive torque	33.7 Nm
Max. radial force at drive shaft	1,100 N
Max. feed force Fx	12,000 N
No-load driving torque	0.6 Nm
Reference value for working load, horizontal	1,200 kg
Reference value for working load, vertical	1,200 kg
Mass moment of inertia JH per meter of stroke	7.8147 kgcm ²
Mass moment of inertia JL per kg of working load	0.05699 kgcm ²
Mass moment of inertia, JO	1.6478 kgcm ²
Moving mass with 0 mm stroke	5,300 g
Additional mass factor per 10 mm of stroke	103 g
Basic weight for 0 mm stroke	7,393 g
Additional weight per 10 mm stroke	155 g
Mounting type	with internal (female) thread or accessories
Interface code, actuator	D80
Materials note	Conforms to RoHS

Feature	Value
Material cover	Coated die-cast aluminium
Material piston rod	High alloy steel, non-corrosive
Material screws	Galvanized steel
Material spindle nut	Roller bearing steel
Material spindle	Roller bearing steel
Material cylinder barrel	Smooth-anodised wrought aluminium alloy