


Bus node CTEU-PN-EX1C

Part number: 8107589

FESTO



Data sheet

Feature	Value
Protocol	PROFINET
Dimensions W x L x H	40 mm x 91 mm x 50 mm
Grid dimension	40 mm
Mounting type	On electrical interface On electrical connection block
Product weight	93 g
Ambient temperature	-5 ... 50 °C
Storage temperature	-20 ... 70 °C
Protection class	IP65 IP67
Note on degree of protection	in assembled condition Unused connections sealed
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364 zone III
CE symbol (see declaration of conformity)	according to EU-EMV guideline in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Authorization	RCM Mark c UL us - Listed (OL)
Certificate issuing department	UL E239998
Materials note	Conforms to RoHS
Material housing	PA
Product-specific LED display	PS: operating voltage for electronics and load supply X1: System status module I port 1 X2: System status module I port 2
Bus-specific LED display	NF: Network error TP1: network active, port 1 TP2: network active, port 2
Diagnosis	Communication error System diagnostics Undervoltage
Fieldbus interface	Ethernet
Fieldbus interface, protocol	PROFINET RT
Fieldbus interface, type of connection	2x socket
Fieldbus interface, connection technology	M12x1, D-coded in accordance with EN 61076-2-101
Fieldbus interface, number of pins/wires	4
Fieldbus interface, electrical isolation	Yes
Fieldbus interface, transmission rate	100 Mbit/s
Maximum address volume for inputs	64 Byte
Maximum address volume for outputs	64 Byte
Internal cycle time	1 ms per 1 byte of user data
Configuration support	GSDML file
Additional functions	Conformance class C Fast Start Up (FSU) LLDP

Feature	Value
	MRP PROFINET IRT PROFenergy SNMP Shared device Web servers
Power supply, function	Electronics and load
Power supply, type of connection	Plug
Power supply, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Power supply, number of pins/wires	5
Operating voltage range DC	18 ... 30 V
Nominal operating voltage DC	24 V
Max. power supply	4 A
Intrinsic current consumption at operating voltage	Typically 80 mA