


Axial kit EAMM-A-M80-80G

Part number: 8063565

FESTO



Data sheet

Feature	Value
Assembly position	Any
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	-10 ... 60 °C
Transferable torque	60 Nm
Product weight	846 g
Interface code, actuator	M80
Interface code, motor in	80G
Materials note	Conforms to RoHS