


Cylinder with holding brake


DFLC-63- -

Part number: 8073332

FESTO



Exemplary representation



Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Stroke	10 ... 2,000 mm
Piston diameter	63 mm
Piston rod thread	M16x1,5
Based on the standard	ISO 15552 (previously also VDMA 24652, ISO 6431, NF E49 003.1, UNI 10290)
Cushioning	PPV: Pneumatic cushioning adjustable at both ends
Assembly position	Any
Type of clamping with direction of action	at both ends Clamping with spring, release with compressed air
Piston-rod end	Male thread
Design structure	Piston Piston rod Profile barrel
Position detection	For proximity sensor
Variants	Single-ended piston rod
Safety function	Holding and stopping a movement
Performance level (PL)	Stopping, holding, blocking a movement/category 1, Performance Level c
Operating pressure MPa	0.06 ... 0.8 MPa
Working pressure	0.6 ... 8 bar
Operating pressure	8.7 ... 116 psi
Max. permissible test pressure	8 bar
Minimum release pressure	3.8 bar
Mode of operation	double-acting
Authorization	TÜV
CE symbol (see declaration of conformity)	according to EU-Ex protection guideline (ATEX) according to EU machines guideline
UKCA marking (see declaration of conformity)	To UK EX instructions To UK instructions for machines
Certificate issuing department	TÜV CA 697
ATEX category Gas	II 2G
ATEX category Dust	II 2D
Explosion ignition protection type Gas	Ex h IIC T4 Gb
Explosion ignition protection type Dust	Ex h IIIC T120°C Db
Explosion-proof ambient temperature	-20°C ≤ Ta ≤ +60°C
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-20 ... 80 °C
Cushioning length	22 mm
Static holding force	3,300 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), retracting	1,682 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance	1,870 N
Moving mass with 0 mm stroke	955 g
Additional mass factor per 10 mm of stroke	25 g

Feature	Value
Basic weight for 0 mm stroke	6,185 g
Additional weight per 10 mm stroke	62 g
Mounting type	with internal (female) thread with accessories
Release connection, clamping unit	G1/8
Pneumatic connection	G3/8
Materials note	Conforms to RoHS
Material cover	Aluminum die cast Wrought Aluminum alloy
Material seals	NBR TPE-U(PU)
Material housing	Steel
Material piston rod	Hard-chrome-plated steel
Material cylinder barrel	Smooth-anodised wrought aluminium alloy