

# Shock absorber DYEF-G8-M6-Y1-F1A

Part number: 8131072

FESTO



## Data sheet

Feature	Value
Size	M6
Stroke	1.5 mm
Cushioning	P cushioning without metal fixed stop
Assembly position	Any
Position detection	No
Variants	Recommended for production facilities for the manufacture of lithium-ion batteries
Max. impact speed	0.8 m/s
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-10 ... 60 °C
Cushioning length	1.5 mm
Max. tightening torque	1 Nm
Max. energy consumption per stroke	0.08 J
Product weight	11.7 g
Mounting type	with threaded sleeve
Materials note	Conforms to RoHS
Material seals	NBR
Material housing	High alloy steel