


Adapter plate

VABA-C13-100-2-F90-G12

Part number: 8141665

FESTO



Data sheet

Feature	Value
Size	1200 2300
Assembly position	Any
Design structure	Adapter for rotary actuator
Valve connection conforms to standard	VDI/VDE 3847-2
Operating pressure MPa	0 ... 0.9 MPa
Working pressure	0 ... 9 bar
Operating medium	Compressed air to ISO 8573-1:2010 [7:7:-] Inert gases
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance classification CRC	3 - High corrosion stress
PWIS conformity	VDMA24364 zone III
Medium temperature	-40 ... 80 °C
Ambient temperature	-40 ... 80 °C
Product weight	3,140 g
Mounting type	with accessories
Pneumatic connection	Sub-base design, airing
Pneumatic connection, port 1	G1/2
Pneumatic connection, port 3	G1/2
Materials note	Conforms to RoHS
Material cover	Smooth-anodised wrought aluminium alloy (20 µm)
Material seals	EPDM NBR
Material housing	Smooth-anodised wrought aluminium alloy (20 µm)
Material screws	High alloy steel, non-corrosive