


# Parallel kit EAMM-U-45-V32-38AA-63

Part number: 8092623

FESTO



## Data sheet

Feature	Value
Size	45
Center-to-center distance	63 mm
Assembly position	Any
Gear unit ratio	1:1
Max. speed	3,600 1/min
PWIS conformity	VDMA24364 zone III
Storage temperature	-20 ... 60 °C
Relative air humidity	0 - 95 %
Protection class	IP40
Ambient temperature	0 ... 50 °C
Mass moment of inertia	4.35 kgmm <sup>2</sup>
No-load driving torque	0.05 Nm
Transferable torque	1 Nm
Product weight	259 g
Interface code, actuator	V32
Interface code, motor in	38AA
Materials note	Conforms to RoHS