


Reductor EMGA-60-P-G12-EAS-60

Cod: 8141736

FESTO



Fisa tehnica

| Caracteristica | valoare |
|--|-------------------------|
| Transmisie flansa | 60 mm |
| Motor cu flansa | 60 mm |
| Joc de rasucire | 0,2 deg |
| tipul reductorului | Angrenaj planetar |
| Raport de transmisie | 12:1 |
| Viteza maxima de intrare | 13.000 1/min |
| Temperatura de operare reductor | -25 ... 90 °C |
| Conformitatea PWIS | VDMA24364-B2-L |
| Tip de protectie | IP54 |
| Cuplu de actionare continua | 44 Nm |
| Momentul de inertie al angrenajului | 0,138 kgcm ² |
| Cuplu maxim iesire | 70 Nm |
| Eficienta maxima | 96 % |
| rigiditate la torsiune | 2,8 Nm/arcmin |
| Greutate produs | 1.100 g |
| Interfata reductor arbore de iesire | 60H |
| Interfata reductor arbore de antrenare | 60P |
| Indicatie material | conform RoHS |