



技術參數

特性	值
通訊協定	AS-Interface
設計結構	T-distributor with cables on both sides
Distributor type	2 to 1
附加功能	Connecting the programming device to an ASInterface component via AS-i flat cable
Cable identification	Without inscription label holder
Electrical connection 1, function	Field device side
Electrical connection 1, design	有角的
Electrical connection 1, connection type	插頭插座
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	AS-Interface
Electrical connection 1, number of pins/wires	2
Electrical connection 1, occupied pins/wires	2
Electrical connection 1, type of mounting	Plug-in
Electrical connection 2, function	Field device side
Electrical connection 2, design	圓形
Electrical connection 2, connection type	插頭插座
Electrical connection 2, cable outlet	直的
Electrical connection 2, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 2, number of pins/wires	4
Electrical connection 2, occupied pins/wires	2
Electrical connection 2, type of mounting	Plug-in
Electrical connection 3, function	Controller side
Electrical connection 3, design	圓形
Electrical connection 3, connection type	插頭
Electrical connection 3, cable outlet	Angled
Electrical connection 3, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection 3, number of pins/wires	4
Electrical connection 3, occupied pins/wires	2
Electrical connection 3, type of mounting	Plug-in
工作電壓範圍 DC	0 ... 48 V
工作電壓範圍 AC	0 ... 48 V
在40°C時的可接受電流負載	3 A
浪湧強度	0.5 kV
Cable length 1	2.4 m
Cable length 2	0.1 m
電纜屬性	標準
電纜的測試條件	視需求的測試條件
電纜結構	2x1,5
導體的額定截面	1.5 mm ²
防護等級	IP20
Note on degree of protection	裝配狀態
環境溫度	-40 ... 85 °C
Ambient temperature with flexible cable installation	-25 ... 80 °C
CE 符號 (參見符合的標準)	in accordance with EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions

特性	值
PWIS conformity	VDMA24364-B2-L
材料備註	符合 RoHS
污染程度	2
Material cable sheath	橡膠化合物
電纜外套顏色	黃色
外殼顏色	黑色