


# Vacuum generator OVTL

Part number: 8103599

FESTO



Exemplary representation

## Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Nominal size, Laval nozzle	0.45 ... 0.95 mm
Grid dimension	10 ... 15 mm
Design, silencer	open
No. of device positions	2 ... 8 mm
Assembly position	Any
Ejector characteristic	High suction flow rate High vacuum Standard
Grade of filtration	40 µm
Manual override	Pushing
Integrated function	Ejector pulse, electrical Flow control valve Pressure sensor Pressure transmitter Electrical on-off valve Filter Open silencer
Design structure	Connection position on both sides Connection position on the side
Switching element function	N/C or N/O contact, switchable
Switching function	Freely programmable
Valve function	closed
Measurement method	Piezoresistive pressure sensor Piezoresistive pressure sensor with display
Type of display	LED display 2-digit
Setting options	IO-Link Teach-In Via display and buttons
Working pressure for max. suction rate	3 ... 6 bar
Operating pressure MPa	0.2 ... 0.7 MPa
Working pressure	2 ... 7 bar
Operating pressure	29 ... 101.5 psi
Working pressure for max. vacuum	3.8 ... 4.5 bar
Max. vacuum	89 ... 92 %
Nominal operating pressure	0.4 MPa
Nominal working pressure	4 bar
Nominal operating pressure (psi)	58 psi
Max. suction rate with respect to atmosphere	4 ... 45 l/min
Air supply time at nominal operating pressure with ejector pulse	0.4 ... 2 s
Analog output	0 - 10 V 1 - 5 V
Operating voltage range DC	21.6 ... 26.4 V
Duty cycle	100 %

<b>Feature</b>	<b>Value</b>
Switch output	PNP/NPN, switchable
Characteristic coil data	24 V DC: 1 W
Authorization	c UL us - Listed (OL)
CE symbol (see declaration of conformity)	according to EU-EMV guideline
UKCA marking (see declaration of conformity)	To UK instructions for EMC
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B1/B2-L
Medium temperature	0 ... 50 °C
Noise level at nominal operating pressure	52 ... 68 dB(A)
Protection class	IP40
Ambient temperature	0 ... 50 °C
Product weight	118 ... 890 g
Operating voltage range, DC sensor	10 ... 30 V
Pressure measurement range	-0.1 ... 0 MPa
Pressure measuring range	-1 ... 0 bar
Pressure measurement range	-14.5 ... 0 psi
Electrical connection, input, function	Ejector pulse Vacuum generation
Electrical connection, input, connection type	2x plug
Electrical connection, input, connection technology	Connection pattern H
Electrical connection, input, number of pins/wires	2
Electrical connection, input, type of mounting	Snap-in locking
Electrical connection, output, function	Sensor
Electrical connection, output, connection type	Cable
Electrical connection, output, connection technology	Open end
Electrical connection, output, number of pins/wires	3
Cable attribute	Suitable for energy chains
Cable diameter	2.9 mm
Cable diameter tolerance	± 0,1 mm
Cable length	2.5 m
Nominal conductor cross-section	0.14 mm <sup>2</sup>
Mounting type	with through hole
Pneumatic connection, port 1	Female thread G1/8 For tubing outside diameter 6 mm For tubing outside diameter 8 mm
Pneumatic connection, port 3	Open silencer For tubing outside diameter 4 mm For tubing outside diameter 6 mm
Vacuum connection	For tubing outside diameter 3 mm For tubing outside diameter 4 mm For tubing outside diameter 6 mm
Cable sheath color	Grey
Material of connecting thread	POM
Materials note	Conforms to RoHS
Material of connecting plate	Wrought Aluminum alloy
Material seals	NBR
Material receiver nozzle	POM
Material filter	POM
Material housing	PA-reinforced
Material hollow bolt	Wrought Aluminum alloy
Material cable sheath	PVC
Material adjusting screw	Steel
Material silencer	PA-reinforced
Material screws	Steel
Material transmitter nozzle	Wrought Aluminum alloy
Material fitting	Nickel-plated brass