


pancake cylinder
DPCA-...-...-3/4"- -
 Part number: 8104872



Exemplary representation

Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Stroke	0.0625 ... 4 "
Piston diameter	3/4"
Piston rod thread	10-32 UNF-2B 10-32 UNF-2A
Cushioning	No cushioning P: Flexible cushioning rings/plates at both ends Elastic cushioning rings/plates, at front Elastic cushioning rings/plates, at rear
Assembly position	Any
Mode of operation	double-acting single-acting pushing action pulling action
Piston-rod end	Male thread Female thread
Design structure	Piston Piston rod Cylinder barrel
Position detection	For proximity sensor
Variants	Increased chemical resistance Through piston rod Through, hollow piston rod Additional PTFE piston guide
Protection against torque/guide	Piston guide pin
Working pressure	15 ... 150 Psi
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364 zone III
Ambient temperature	-25 ... 250 °F
Product weight	0.14 ... 0.81 Pound
Mounting type	with swivelling rod eye on end cap rotated 90° with swivelling rod eye on end cap with swivelling fork on end cap rotated 90° with swivelling fork on end cap with through hole with accessories Optional
Pneumatic connection	Female thread M5 Female thread 10-32 UNF-2B
Materials note	Conforms to RoHS
Material cover	Wrought Aluminum alloy
Material of dynamic seals	FPM NBR
Material piston rod	High alloy steel
Material cylinder barrel	Wrought Aluminum alloy