


Parallel kit EAMM-U-110-S95-90GA-207

Part number: 8105907

FESTO



Data sheet

| Feature | Value |
|--------------------------|-----------------------|
| Size | 110 |
| Assembly position | Any |
| Max. speed | 5,000 1/min |
| PWIS conformity | VDMA24364-B2-L |
| Storage temperature | -25 ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Protection class | IP40 |
| Ambient temperature | -10 ... 60 °C |
| Mass moment of inertia | 799 kgmm ² |
| No-load driving torque | 0.3 Nm |
| Transferable torque | 9.5 Nm |
| Product weight | 6,900 g |
| Interface code, actuator | S95 |
| Interface code, motor in | 90GA |
| Materials note | Conforms to RoHS |