

密封圈

NPAS-C1-R-G38-P-FD-P10

料號: 2652519

FESTO



技術參數

特性	值
容器尺寸	10
裝配位置	任何
Operating pressure for entire temperature range	-0.095 ... 1.2 MPa
操作壓力的完整溫度範圍	-0.95 ... 12 bar
Operating pressure for entire temperature range	-13.775 ... 174 psi
操作介質	壓縮空氣符合 ISO8573-1:2010 [7:-:-] Water (liquid, free of ice) Water vapour
注意: 操作和嚮導介質	潤滑操作可行
PWIS conformity	VDMA24364-B2-L
Food-safe	See Supplementary material information
環境溫度	-20 ... 120 °C
額定鎖緊扭矩	35 Nm
額定擰緊扭矩公差	± 10 %
產品重量	0.15 g
氣壓連接	G3/8
材料備註	符合 RoHS
Material seals	PEEK