



# 止動氣壓缸 EFSD-50-PV-M12

料號: 2942446

FESTO



## 技術參數

特性	值
設計結構	Electric stopper cylinder
尺寸	50
裝配位置	任何
位置檢測	具霍爾感測器
耐腐蝕等級 CRC	1 - Low corrosion stress
環境溫度	-10 ... 60 °C
儲藏溫度	-20 ... 60 °C
相對空氣濕度	0 - 95 % 非冷凝
緩衝長度	17.5 mm
產品重量	800 g
最大循環頻率	0.33 Hz
安裝類型	With mounting kit
授權	RCM Mark
材料備註	符合 RoHS
PWIS conformity	VDMA24364 zone III
Material cover	PA PA-加強
Material seals	NBR
Material housing	Hard anodised wrought aluminium alloy
Material piston rod	高合金鋼, 耐腐蝕
Material screws	Coated steel
最大電流消耗	2 A
額定工作電壓 DC	24 V
容許的電壓波動	+/- 15 %
馬達類型	步進馬達
KC mark	KC-EMV
CE 符號 (參見符合的標準)	根據 EU-EMV 指導原則
UKCA marking (see declaration of conformity)	To UK instructions for EMC
防護等級	IP40
最大行列長度	30 m
預備狀態顯示	LED
Electrical connection for actuator, connection type	插頭
Electrical connection for actuator, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection for actuator, number of pins/wires	5
Electrical connection for sensor, connection type	插頭
Electrical connection for sensor, connection technology	M12x1, A-coded in accordance with EN 61076-2-101
Electrical connection for sensor, number of pins/wires	5