

連接電纜

KMP6-09P-8-2,5



料號: 531184

Classic - nicht für Neukonstruktionen verwenden

用於小型閥，具 Sub-D 插頭，9-pin，用於 8 個線圈。

Modern alternatives can be found by entering the first four characters of the type code in the search field.

FESTO



技術參數

| 特性 | 值 |
|--|---|
| 符合標準 | DIN 41652 |
| Cable identification | Without inscription label holder |
| 連接頻率 | 50 |
| 產品重量 | 248 g |
| Electrical connection 1, function | Field device side |
| Electrical connection 1, design | 有角的 |
| Electrical connection 1, connection type | 插頭插座 |
| Electrical connection 1, cable outlet | 直的 |
| Electrical connection 1, connection technology | Sub-D |
| Electrical connection 1, number of pins/wires | 9 |
| Electrical connection 1, occupied pins/wires | 9 |
| Electrical connection 1, type of mounting | 2 screws 4-40 UNC |
| Electrical connection 2, function | Controller side |
| Electrical connection 2, connection type | 電纜 |
| Electrical connection 2, connection technology | 開放式終端 |
| Electrical connection 2, number of pins/wires | 9 |
| Electrical connection 2, occupied pins/wires | 9 |
| 工作電壓範圍 DC | 0 ... 30 V |
| 額定工作電壓 DC | 24 V |
| 在40°C時的可接受電流負載 | 2.8 A |
| 浪湧強度 | 1 kV |
| 電纜長度 | 2.5 m |
| 電纜屬性 | 標準 |
| 電纜的測試條件 | 視需求的測試條件 |
| Bending radius, fixed cable installation | >= 76 mm |
| Bending radius, flexible cable installation | >= 114 mm |
| 電纜直徑 | 7.6 mm |
| 電纜直徑公差 | ± 0,25 mm |
| 電纜結構 | 8x0,34+1x0,5 |
| 導體的額定截面 | 0.34 mm ² 0.5 mm ² |
| 導線末端 | Cut off bluntly |
| 防護等級 | IP40 |
| Note on degree of protection | 裝配狀態 |
| 環境溫度 | -25 ... 70 °C |
| Ambient temperature with flexible cable installation | -5 ... 70 °C |
| 儲藏溫度 | -25 ... 75 °C |
| CE 符號 (參見符合的標準) | in accordance with EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions |
| PWIS conformity | VDMA24364-B2-L |
| 材料備註 | 符合 RoHS |
| 污染程度 | 2 |

| 特性 | 值 |
|-----------------------------|--------------------------|
| Material cable sheath | PVC |
| 電纜外套顏色 | 灰色 |
| Material housing | PBT-加強 |
| 外殼顏色 | 灰色 |
| Material screw-type lock | Nickel-plated brass |
| Material electrical contact | Gold-plated copper alloy |