



保護罩 VMPA-KMS-H

料號: 533198

FESTO

用於多針腳插頭連接至閩島 MPA-S.



技術參數

特性	值
基於標準	DIN 41652
連接頻率	50
產品重量	71 g
電氣連接	插頭/插座
Electrical connection 1, function	Field device side
Electrical connection 1, design	有角的
Electrical connection 1, connection type	插頭插座
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	25
Electrical connection 1, type of mounting	3x M3 screws
Electrical connection 2, function	Controller side
Electrical connection 2, connection technology	Crimp contacts
工作電壓範圍 DC	0 ... 30 V
額定工作電壓 DC	24 V
額定工作電壓, AC	3 V
浪湧強度	1 kV
電纜直徑	6 ... 12 mm
防護等級	IP65 符合 IEC 60529
Note on degree of protection	裝配狀態
環境溫度	-25 ... 80 °C
PWIS conformity	VDMA24364-B2-L
材料備註	符合 RoHS
污染程度	3
耐腐蝕等級 CRC	2 - Moderate corrosion stress
Material housing	PA
外殼顏色	灰色
Material of union nut	PA
Material seals	CR NBR
Material electrical contact	Gold-plated copper alloy