



馬達電纜 NEBM-S1G9-E-15-LE6

料號: 550742

☆ Kernprogramm

適用於伺服馬達EMMS-ST...

FESTO



技術參數

| 特性 | 值 |
|--|----------------------------------|
| 電纜屬性 | 適合於拖鏈 |
| 工作電壓範圍 DC | 0 ... 72 V |
| 防護等級 | IP65 |
| Note on degree of protection | 裝配狀態 |
| Ambient temperature with flexible cable installation | -40 ... 70 °C |
| 環境溫度 | -40 ... 70 °C |
| Bending radius, flexible cable installation | >= 58 mm |
| Electrical connection 1, function | Field device side |
| Electrical connection 1, connection type | 插頭插座 |
| Electrical connection 1, cable outlet | 直的 |
| Electrical connection 1, design | 有角的 |
| Electrical connection 1, connection technology | Sub-D |
| Electrical connection 1, number of pins/wires | 9 |
| Electrical connection 1, occupied pins/wires | 6 |
| Electrical connection 2, function | Controller side |
| Electrical connection 2, connection type | 電纜 |
| Electrical connection 2, connection technology | 開放式終端 |
| Electrical connection 2, number of pins/wires | 7 |
| Electrical connection 2, occupied pins/wires | 6 |
| 導線末端 | 導線末端套圈 |
| 電纜結構 | 7x0,34 已屏蔽 |
| 電纜直徑 | 8 mm |
| 電纜長度 | 15 m |
| 導體的額定截面 | 0.34 mm ² |
| Cable identification | Without inscription label holder |
| 電纜外套顏色 | 灰色 |
| 材料備註 | 符合 RoHS |
| 電纜護套的材料訊息 | TPE-U(PUR) |